



TUBULAR RIPPLE

White Light's 2000w tubular ripple effect is used free standing close to the bottom of a cyc or hung to produce a moving ripple motion. Gel can also be added to provide a more realistic coloured effect. This effect requires a non dimmed circuit to power the rotating tube together with a normal dimmer circuit for the lamp itself.

Light and power supply system

| | | | |
|---------|-------------------------|-------------------|-----------|
| Voltage | 240V 50Hz | Average life span | 500 Hours |
| Power | 1000w x 2 (2000w total) | Lamp | 1000w QI |

Appearance parameters

| | | | |
|-----------|------------|------------|-------------------|
| Structure | Steel case | Size | 550 x 245 x 210mm |
| IP Rate | IP20 | Net weight | 13.35 Kg |

